

NH-4

Mass 30g

The pins of the electrodes

in the tube with 2 plates:

- 1-figure 4
- 2-figure 6
- 3-figure 8
- 4-screen
- 5-figure 9
- 6-figure 7
- 7-is not connected
- 8-figure 0
- 9-figure 2
- 10-second plate
- 11-figure 3
- 12-figure 5
- 13-first plate
- 14-figure 1

in the tube with 1 plate :

- 1-figure 4
- 2-figure 6
- 3-figure 8
- 4- is not connected
- 5-figure 9
- 6-figure 7
- 7-is not connected
- 8-figure 0
- 9-figure 2
- 10- is not connected
- 11-figure 3
- 12-figure 5
- 13- plate
- 14-figure 1

Technical specifications:

- Brightness $\geq 100 \text{Kd/m}^2$
- Power supply voltage $\geq 200 \text{V}$
- Lighting voltage $\leq 170 \text{V}$
- Operating voltage $\leq 160 \text{V}$
- The voltage of indication $\leq 2.5 \text{mA}$
- The operation voltage 2.5-3mA
- Capacity of work $\geq 1000 \text{hours}$

